

I.W.3



INDIRECTLY-HEATED FULL-WAVE RECTIFIER

OPERATING DATA.

Heater Voltage 4.0 V.
Heater Current.. .. 2.4 A.
Max. Anode Voltage

350-0-350 V. r.m.s.

OUTPUT.

Maximum rectified current
120 mA D.C. at 350 V.

PRICE 10/6

I.W.4/350 QUICK-HEATING I.H. FULL-WAVE RECTIFIER

OPERATING DATA.

Heater Voltage 4.0 V.
Heater Current.. .. 2.0 A.
Max. Anode Voltage

350-0-350 V. r.m.s.

OUTPUT.

Maximum rectified current
120 mA D.C. at 350 V.

This valve must not be used with indirectly-heated output valves having a heating time greater than 20 seconds. It can be used with the PEN.A4, or any directly-heated output valve.

PRICE 10/6

I.W.4 INDIRECTLY-HEATED FULL-WAVE RECTIFIER

OPERATING DATA.

Heater Voltage 4.0 V.
Heater Current.. .. 2.4 A.
Max. Anode Voltage

500-0-500 V. r.m.s.

OUTPUT.

Maximum rectified current
120 mA D.C. at 500 V.

PRICE 15/-